


实验室配电柜 (甲方提供)


Pe=80KW
Kx=0.80
Cosφ=0.85
Pjs=64KW
Ijs=114.4A

双电源由院方提供并接入



PE
N

消防信号



- 要求:
1. 配电源指示灯
 2. 配工作指示灯
 3. 配电流表 三只
 4. 配电压表 一只
 5. 配电压转换开关
 6. N, PE 推分开, 接线螺栓满足进出线回路数
 7. 柜体选型.

DPN N/16A	L1	ZR-BV2x2.5+E2.5-JDG20	ACC	照明1.0KW
DPN Nvigi-20A/30mA	L2	ZR-BV2x4.0+E4.0-JDG20	WC	插座1.5KW
DPN Nvigi-20A/30mA	L3	ZR-BV2x4.0+E4.0-JDG20	WC	插座1.5KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	插座1.5KW
DPN Nvigi-20A/30mA	L2	ZR-BV2x4.0+E4.0-JDG20	WC	插座1.5KW
DPN Nvigi-20A/30mA	L3	ZR-BV2x4.0+E4.0-JDG20	WC	风机1.8KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	生物安全柜1.5KW
DPN Nvigi-20A/30mA	L2	ZR-BV2x4.0+E4.0-JDG20	WC	超净工作台1.5KW
DPN Nvigi-20A/30mA	L3	ZR-BV2x4.0+E4.0-JDG20	WC	超净工作台1.5KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	培养箱1.5KW
DPN Nvigi-20A/30mA	L2	ZR-BV2x4.0+E4.0-JDG20	WC	培养箱1.5KW
DPN Nvigi-20A/30mA	L3	ZR-BV2x4.0+E4.0-JDG20	WC	培养箱1.5KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	离心机1.5KW
DPN Nvigi-20A/30mA	L2	ZR-BV2x4.0+E4.0-JDG20	WC	离心机1.5KW
DPN Nvigi-20A/30mA	L3	ZR-BV2x4.0+E4.0-JDG20	WC	离心机1.5KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	-80℃冰箱1.3KW
DPN Nvigi-20A/30mA	L2	ZR-BV2x4.0+E4.0-JDG20	WC	-80℃冰箱1.3KW
DPN Nvigi-20A/30mA	L3	ZR-BV2x4.0+E4.0-JDG20	WC	-40℃冰箱1.1KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	恒温水浴1.5KW
DPN Nvigi-20A/30mA	L1	ZR-BV2x4.0+E4.0-JDG20	WC	挂壁空调(预留)1.5KW
C65N-C25/3P		ZR-BV4x4.0+E4.0-JDG25	WC	柜式空调(预留)2.5KW
NSE100N-100A/3P		WDZB-YJY3x35+2x16	CT	AHU1 控制柜 45KW
NSE100N-100A/3P				备用
C65N-C25/3P				备用
DPN N/16A				备用
DPN Nvigi-20A/30mA				备用x2
NSE100N-20A/4P				

消防报警 PR20(3P+N)